



BLEACH WHITE

# BW

## ReLight

UNIVERSAL LIGHT-CURING  
COMPOSITE MATERIAL

SHADE **BW** APPLIED  
FOR RESTORATION OF:



bleached  
teeth



milk  
teeth



Material possesses average transparency level between dentine and enamel, which depends on layer thickness	Material layer thickness, mm	Photopolymerization time, s	
		For LED lamps (1000–2000 mW/cm <sup>2</sup> ), s	For halogen lamps (500–1000 mW/cm <sup>2</sup> ), s
	1.5	10	20

### EXCEPTIONAL HANDLING . SOFT . DURABLE

Shade BW is lighter than the most light B1 shade in VitaClassical scale